

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 31838 ABS A D 50H E B B

Product Code	31838	Grande Plymouth
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	A B C D E M P Q	Clear Acrylic Opal Acrylic Clear Seeded Acrylic Bronze Tone Acrylic Clear Textured Acrylic Opal Polycarbonate Clear Polycarbonate Prismatic Polycarbonate
Socket	D G L R	Medium Mogul LED Induction
Wattage/Source	50H 70H 100H 150H 250H 35S 50S 70S 100S 150S 250S 200I 55R 85R 165R LED	50W MH 70W MH 100W MH 150W MH 250W MH 35W HPS 50W HPS 70W HPS 100W HPS 150W HPS 250W HPS 200W INC 55W Induction 85W Induction 165W Induction LED

31838 Grande Plymouth

Post top

Ordering Guide

Example: 31838 ABS A D 50H E B B

Voltage	E	120V	
	F	208V	
	G	240V	
	H	277V	
Distribution	B	6" Type V Distrib.	
	C	6" Type III Distrib.	
	D	8" Type V Distrib.	
	E	8" Type II Distrib.	
	M	Type III - Cutoff Optic	
	P	Type V - Cutoff Optics	
	T	Type V - Full Cutoff Optic	
	V	Type V - Cone	
	N	None	
Photoeye	B	Button Eye	*1
	R	Twist-Lock	
	N	None	

*1 Button Eye (B) only available in 120V (E).

*2 (S) and (T) optics only available with (GF) clear glass lens.

Specifications

CONSTRUCTION:

Cast aluminum finial, cap, and neck. Cast aluminum square hinged roof. Cast aluminum square cage. 3/8" O.D. Wireway tubing concealed in cage corner. Cast aluminum post fitter slips over 3" dia. post or tenon.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast and component parts mounted inside three-piece cast aluminum moisture proof ballast compartment with hinged access door and slide-out ballast tray. (Customer must specify wattage and voltage.)

MOUNTING:

Fixture mounts to 3" dia. post or tenon.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

38 5/8"

Width:

14 3/4"

Fitter:

3" I.D.

EPA:

1.60

Max. Weight:

44 lbs.

