




Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



BEZEL 16 WITH LOW PROFILE ADAPTER



BEZEL 16 WITH HINGED ADAPTER



Ordering Information

Catalog No.	Finishes	Mounting	Lamps
8217WH	Matte White	All Lytespan Track Systems	60W PAR16 Sylvania lamps only
8217BK	Matte Black		

Features

- Shade Attachment:** Zinc plated and painted C.R. steel. Bayonet fitting.
- Shade:** Die-cast aluminum.
- Front Bezel:** High temperature Ultem®. Integral color. Removes extraneous spill light.
- Shade Rear Vents:** Aligns with Adapter's vents for effective air circulation.
- Color Accent Ring:** Silicone rubber.

Labels

UL; I.B.E.W.

Ultem® is a trademark of General Electric.

Options & Accessories

2" Beam Smoother and Beam Elongator. All require Accessory Holder 8591. See Lightolier Specification Sheets AF2LF and AF2AS.
 Do not use with AL2HC louver.

Finish

All painted finishes baked enamel.

8217WH Par-Tech


Bezel 16 Shade

Lighting Data

Aiming Angle

- L** Beam Length
- W** Beam Width
- C** Distance to center beam
- D** Distance
- A** Aiming Angle
- FC** Footcandles

L and **W** are the outer points where the candle power drops to 50% of the maximum. **FC** are the initial footcandles at the center of the beam.



LAMP 0° AIMING ANGLE A=30° AIMING ANGLE A=45° AIMING ANGLE A=60° AIMING ANGLE

