PHILIPS

Ceiling light

Functional

CL702

White

RF Dimming

6922341923739



Set your desired ambiance at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment

Easy to experience
- Enhance your moment Tunable with memory function
- 10s time delay light off with remote control

Premium quality
- EyeComfort - light that's easy on the eyes

Control
- Tunable with wall switch
- 4 pre-set scenes
- Auto shutdown after 60 mins
- Convenient brightness control Linear dimming function (remote control not included)

Highlights

Enhance your moment Tunable with memory function
Memorize your favorite tunings of different light settings to easily find your perfect level of illumination.

10s time delay light off with remote control
The 10 second delay gives you time to leave the room once you've turned out the light with your remote.

Eyecomfort
Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they
meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable with wall switch
An easy-to-use wall switch allows you to shift between different light colors.

4 pre-set scenes
Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Auto shutdown after 60 mins
When sleep mode is on, the light will automatically go out after 60 minutes. No more getting up in the middle of the night just to witch the light off.

Convenient brightness control Linear dimming function (remote control not included)
Lets you smoothly shift between different brightness levels to find the perfect mood.

Specifications

Bulb characteristics
- Intended use: Indoor

Design and finishing
- Color: White
- Material: Metal, Plastic

Durability
- Number of switch cycles: 15,000

Extra feature/accessory incl.
- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

Light characteristics
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous
- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics
- Lamp current: 285 mA
- Efficacy: 81 lm/W

Product dimensions and weight
- Net weight: 3.2 kg
- Height: 8.3 cm
- Length: 57.2 cm
- Width: 57.2 cm

Service
- Warranty: 1 year(s)

Technical specifications
- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 4500
- Light color: 2700-6500
- Mains power: AC 220-240
- Fixture dimmable: RF Dim - Do not use with dimmer
- LED: Yes
- Wattage bulb included: 55
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight
- Net weight: 3.08 kg
- Gross weight: 4.36 kg
- Height: 0
- Length: 0
- Width: 0
- Material number (12NC): 929002638509

Issue date: 2024-01-15
Version: 0.78

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com