

# PHILIPS

Recessed spot light

myLiving

Magnetic Sys

Black



6922341954719



## Smart lighting for you daily living

Fashion concise line draw the outline of the environment light path. In order to create a high quality space with Non-center Piece design, Philips launches brand new Magnetic Sys products. With the unique patent GentleBright technology, using professional 2-zone diffuser design to precise control of light, filter stray light effectively, reduce glare and bring comfortable and bright pure light! Recessed trimless tracker can be collocated with high flexibility, multi-module application adapt to unlimited installation scenario, which shows off fashion versatile highlight exclusive sense of life, leading contemporary fashion lighting, and decorate the beauty of modern space!

### Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

### Match your interior

- Super slim design

### Light effect

- Bright light with uniform distribution

# Highlights

## Create a stylish atmosphere

This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambiance you have always desired.

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Black
- Material: Metal, Plastic
- Housing Color: Black
- Housing Material: Metal–Plastic
- Optical cover finish: Mask (anti-glare)
- Optical cover material: Polycarbonate

## Durability

- Number of switch cycles: 12,500
- Ambient temperature range: -20 to +40 °C

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Guarantee

- Warranty period: 1 years

## Light characteristics

- Beam angle: 90 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 90
- Luminous flux tolerance: +/-10%
- Constant light output: No
- Correlated Color Temperature (Nom): 3000
- Initial chromaticity: (  $u$  ,  $v$  ) <5
- Light source replaceable: Yes
- Luminaire light beam spread: 90°
- Luminous Efficacy (rated) (Nom): 80.00 lm/W
- Luminous Flux: 1,000 lm
- Optic material: Polycarbonate
- Optic type: Beam angle 90°
- Reflector material: -

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Track Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 260 mA
- Efficacy: 80 lm/W
- EU RoHS compliant: Yes

## Power

- Input Voltage: 48
- Power Factor (Fraction): -

## Power consumption

- Power Consumption: 12.5 W
- Power consumption tolerance: +/-10%

**Product dimensions and weight**

- Net weight: 0.26 kg
- Height: 4.3 cm
- Length: 44.4 cm
- Width: 2.2 cm
- Overall height: 43 mm
- Overall length: 444 mm
- Overall width: 22 mm

**Service**

- Warranty: 3 year(s)

**Technical specifications**

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 1000
- Light color: 3000
- Mains power: 48
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12.5
- IP code: IP20
- Class of protection: Class III
- Connection: Connection unit 2-pole
- Dimmable: No
- Driver/power unit/transformer: Power supply unit external (On/Off)
- Driver included: No
- Fixation material: Polyamide
- Flammability mark: For mounting on normally flammable surfaces
- Glow-wire test: Temperature 650 °C, duration 30 s
- Ingress protection code: IP20 | Finger-protected
- Line Frequency: –
- Mech. impact protection code: IK03 | 0.3 J
- Number of gear units: 1 unit
- Protection class IEC: Safety class III
- Suitable for random switching: No

**Packaging dimensions and weight**

- EAN/UPC – product: 6922341954719
- Net weight: 0.26 kg
- Gross weight: 0.29 kg
- Height: 49.5 cm
- Length: 2.6 cm
- Width: 4.7 cm
- Material number (12NC): 929003207010



Issue date: 2024-02-05  
Version: 0.134

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)