

PHILIPS

Ceiling light

Functional

CL850

Silver

Dim

6922341969539



Set your desired ambiance at your fingertips

Create the right ambience every time. Our all-in-one Premium ceiling light gives you a sophisticated yet easy-to-use remote control to select different light settings while managing multi-layer light changes. With its attractive design, you can set the scene in style

Sustainable light solutions

- High quality LED light

Easy to experience

- Easy installation
- Enhance your moment Tunable with memory function

Light effect

- Multiple layered visual effect Dynamic tiered design

Premium quality

- Premium faceted crystals for sparkling light effect

Control

- 4 pre-set scenes
- Remote control provides easy control of light settings up to 10M
- Multi light zone control

Highlights

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Enhance your moment Tunable with memory function

Memorize your favorite tunings of different light settings to easily find your perfect level of illumination.

Multiple layered visual effect Dynamic tiered design

This dynamic tiered design makes for a striking impression that adds a creative touch to your rooms.

Premium faceted crystals for sparkling light effect

Faceted crystals a touch of refined, vintage charm to your space.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Remote control provides easy control of light settings up to 10M

Turn lights on or off or change brightness and color from up to 10m away with this remote control.

Multi light zone control

Allows you to adjust the brightness and/or color temperature in different light zones of the same luminaire to create a personalized light scene.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: Silver
- Material: Metal

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 300 mA
- Efficacy: 75 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 4.7 kg
- Height: 9.4 cm
- Length: 65.5 cm
- Width: 65.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 655 mm
- Total lumen output fixture: 4500
- Light color: 2700-6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 60
- IP code: IP20

- Class of protection: Class I

Packaging dimensions and weight

- Net weight: 4.7 kg
- Gross weight: 5.15 kg
- Height: 0
- Length: 0
- Width: 0
- Material number (12NC):
929003246509



Issue date: 2024-01-18
Version: 0.63

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com