

All rights are reserved. Reproduction in whole or part is prohibited without the written consent of the copyright owner.


Signify Holding







CE ROHS IP40
















SYMBOL	MEANING
[SONEO Hz	LAMP SUITABLE FOR 50Hz OR 60Hz OPERATION
**	NEED TO BE USED IN DRY CONDITIONS OR IN A LUMINAIRE THAT PROVIDES PROTECTION

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.

11/2018		
www.philips.com/lighting		

3241 653 83901

Brand	Philips
Product Famil	ly HIB & New Application
Shape	
Wattage	
Template Ref	. NA
SGS number	
	324165383901
Masterdrawin	ng N/A
CRC Ref.	
Barcode No.	N/A
Operator(s)	IDEP
Operator(s)	
VERSION No	, v1
Date in <u>2015</u>	0514
Date amende	d 20181129
	Magenta Yellow Black
Cyan P	Magenta Yellow Black
Diecut	
Date Check	<u> </u>
Check b	riefing Traffic
Artwork do	cument
Legend	Number of colors
12NC	Trapping/Bleed
Barcode	Images hires
Diecut	Jobsizes
	Approval
	•
QC Litho	ographer SGS Shanghai Production
Product I	Manager xiaowen.wang@signify.com

PHILIPS LIGHTING

Die-Cut:	A4	size	正反	面	单	色	印	刷

t Info	2000 12110.	Designer: SH SGS	3 SH 3G3	Duplexbox: 324165383901		Author	Date	Change number	Revision description
		Design date: 2018-11-30		EANI number: N/A	ojul	SH SGS	2018/11/30		
	Description:		sic In	Die-Cut: N/A	ange li				
	TForce LED Road 55-35W E27 730		Ba	Surface treatment: N/A	Ch				
11 0100 EED 11000 00 001V EE7 700				CRC: CRC000					