


Urban

Bracket arm

263DB Arm bracket





Ordering Guide

Example: 263DB ABS Twist-lock

Product Code	263DB	Bracket Arm
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Photo Control	Twist-lock	Twist-lock photocell supplied

Specifications

CONSTRUCTION:

Cast aluminum decorative end cap (removable). Three cast aluminum post caps. 2" dia. aluminum formed arm. Cast aluminum access door. Cast aluminum 4" I.D. post fitter.

FINISH

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Fixture mounts to 4" I.D. post.

WARRANTY:

Three-year limited warranty.

Height: Width: Max. Weight: 33 7/8" 93 1/8"



© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855–486–2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008