

PHILIPS

Indirect light

myLiving

LIGHTSTRIPS 5M RGB

multi color

LED



70102/31/P6



Color your world with light

The Philips LightStrips are the most flexible solution to add a colorful touch of light to your interior. Use the 5 meter version in a coved ceiling, stairs or your kitchen and change colors or effects with the easy to use remote control.

Easy and safe to use

- Safe LED technology
- Protective silicon layer
- Easy-to-use remote control

Let the colors blend naturally into your interior

- Adjust the brightness by using the remote control
- Choose among 30 colors
- Automatic color changing mode

Ultimate flexibility in installation

- Easy to mount with adhesive tape
- Cut to size
- Plug & Play: easy installation

Highlights

Safe LED technology



The LightStrips are safe to touch and use without the risk of open electricity.


Protective silicon layer

Enhanced protection for electrical parts against dust and moisture, even during cleaning.

Easy-to-use remote control

The infrared remote control allows you to control easily the LightStrips while you're relaxing on the sofa or lying on the bed. Use the remote control to turn on/off the light, change color, adjust brightness or choose one of the lighting modes and control the speed.

Dimmable



Adjust the brightness by using the remote control.

Choose among 30 colors

Choose your favorite color and change it any time you like. Or put on a dynamic light effect to create a richer atmosphere. You can even turn it on strobo mode and have a party with friends.

Automatic color changing mode


You can choose different automatic color changing modes and adjust the speed and brightness of the color loop. This by simply pressing the button on the remote control.

Easy to mount



Paste the LightStrips wherever you like thanks to the integrated high quality adhesive strip on the backside.

Cut to size



If your LightStrips do not exactly fit the required application, you can easily cut them to size. Cutting marks on the product indicate where to cut.

Plug & Play: easy installation

The LightStrips are very easy to install and guarantee immediate fun thanks to the plug & play principle. Everything you need is already included in the box and explained in the Quick Start Guide.

Specifications

Design and finishing

- Color: Transparent
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: Yes
- Centerpiece: No

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom, Kitchen
- Style: Expressive
- Type: Downlight & Spots
- EyeComfort: No

Product dimensions & weight

- Height: 1 cm
- Length: 500 cm
- Net weight: 302 kg
- Width: 0.25 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 260
- Light color: RGB
- Mains power: 220–240
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 21
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC – product: 8718696164242
- Net weight: 0.102 kg
- Gross weight: 0.190 kg
- Height: 164.000 mm
- Length: 57.000 mm
- Width: 162.000 mm
- Material number (12NC): 915005517301



Issue date: 2023-11-08
Version: 0.1294

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com