

## DESCRIPTION

Circular and Radial forms are the theme of the Loop Series fixtures. The Loop Circular Sconce/Surface fixture has an angular white acrylic lens turned vertically and encased in a solid metal spinning. Behind the lens is a ring of LED sources providing indirect illumination on the lens. The resulting light effect is a stimulating glow that fades subtly toward the perimeter of the fixture. A wide variety of finish options and LED color temperatures allows the designer to select a look that is right for many different settings.

## SPECIFICATION FEATURES

### Material

Painted aluminum body with a matte white acrylic diffuser.

### Finishes:

ALP (Aluminum Paint)  
 BM (Bronze Metallic)  
 DP (Dark Platinum)  
 GRM (Graphite Metallic)  
 MB (Matte Black)  
 MW (Matte White)  
 CC (Custom Color – Specify)

### LED:

14" L2: 1600 source lumens at max 14W  
 18" L4: 3000 source lumens at max 29W

### Drivers

LED system coupled with electronic driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming standard on all models.

### Installation


The Loop Circular Sconce is designed with an open center backplate with circle strap pattern and additional mounting holes for mounting to many wall surfaces. The position of the j-box is off-set from the center of the fixture – see approximate mounting dimensions on the drawings below. Recommended installation instructions are available on-line.

Catalog #		Type
Project		
Comments		Date
Prepared by		



## AUTOGRAPH COLLECTION LOOP SERIES 865 LOOP SCONCE

## DIMENSIONS



- Diameter: 14"**
- Lumen Output Source Lumens: 1600
  - Wattage: 14w
  - Color Rendering: CRI 83+
  - Correlated Color Temperature: 2700K, 3000K, 3500K, 4000K
  - Rated Life of Lamp (hrs): 50,000
  - Dimming: 0-10V
  - Warranty: 5 year limited warranty on LED components
- Diameter: 18"**
- Lumen Output Source Lumens: 3000
  - Wattage: 29w
  - Color Rendering: CRI 83+
  - Correlated Color Temperature: 2700K, 3000K, 3500K, 4000K
  - Rated Life of Lamp (hrs): 50,000
  - Dimming: 0-10V
  - Warranty: 5 year limited warranty on LED components

## ORDERING INFORMATION

Sample Number: 865-18-W-L4/827-UNV-MV

Series	Size	Mounting Type	LED Lamp		LED Voltage	Finish	Options
			14"	18"			
865 = Loop Circular Sconce	14=14" 18=18"	W=Wall	L2/827	L4/827	UNV (120-277V)	MW=Matte White MB=Matte Black DP= Dark Platinum ALP=Aluminum Paint GRM=Graphite Metallic CC=Custom Color - Specify	RBP =Remote Battery Pack (Max Distance 5')
			L2/830	L4/830			
			L2/835	L4/835			
			L2/840	L4/840			