
LIGHTOLIER

by (s) ignify

Downlighting

Lytening INC 5"

1004SICR Shallow IC/Non-IC Remodeler







Frame-In Kit

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately

Complete 11xture consists of henector frim & 11ame-in kit. Select each separatery.							
Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets						
	Open Downlight						
	Specular Cone	Satin Cone	Baffles	Basic White	Wall Washer	Enclosed Diffuser	
1004SICR	1012 1012NM 1013 1013BK 1013WH 1013CD 1013NM 1013BKNM	1008 1008NM 1010 1010NM	1005 1005WH 1005NM 1005BNM 1076 1076WH	1071	1085*	1024*	*For Non-IC applications only
	1013BKNM 1013CDNM						*For Non-IC applications only

Features

- Housing: .032" (#20 ga.) Aluminum. UL listed convertible IC/NON-IC. Integral retaining spring secures housing to ceilings up to 2" thick. Removable for access to junction box and ceiling plenum. 5 1/2" tall for use in 2" X 6" joist construction and shallow plenum applications.
- 2. Junction Box: 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.).032" (#22 ga.) galvanized steel. UL listed for 90°C supply wire. Suitable for branch circuit wiring supplying connected fixtures. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- 3. **Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.
- Socket: Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 Volt 200°C) leads to junction box.
- 5. Thermal Protector: Meets NEC and U.L. requirements. Located inside housing

Options & Accessories

AirSeal® Kit: LAS56R (required for AirSeal Installation)

Labels

UL (Type IC/NON-IC Convertible, Suitable for Damp Locations)

Complies with Air Leakage Requirements stated in the Model Energy Code and the Washington State Energy Code.

Romex® is a registered trademark of General Cable Industries Inc.



© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008