


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_



### Ordering Guide

Example: BT1 A LED7 NF W S

<b>Product Code</b>	BT1	LED Bullyte
<b>Finish</b>	A H	Black Bronze
<b>Source/Lumens</b>	LED7	7W LED
<b>Optics</b>	NF FL	Narrow Flood Flood
<b>CCT</b>	W	Warm
<b>Shroud</b>	S L	Short Shroud Long Shroud

\*1 Fixture will be shipped with lamp. Lamp not sold separately.

### Specifications

**HOUSING:**

Gasketing is silicone. Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. Fully rotatable shroud, gasketed, cast aluminum. Fasteners are 300 series stainless steel.

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

**OPTICAL ASSEMBLY:**

Clear tempered glass lens.

**LAMPING:**

7W lamp with 25° or 35° beam spread, 25,000 hours life. Color temperature (CCT): Warm White (3,000K nominal). No Mercury. Dimmable. Approximately 460 lumens.

**ELECTRICAL ASSEMBLY:**

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. Fixture is pre-wired with 18 AWG black, white, and ground wires. Step-down transformer reduces line voltage to 12 volts. Transformer is potted/encapsulated and features thermal overload protection. Can be used with energy-efficient halogen lamp.

**WARRANTY:**

Five-year limited warranty.

**CERTIFICATIONS:**

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

<b>Max Width:</b>	<b>Max Length:</b>	<b>Max. Weight:</b>
3 7/8" (98mm)	8 3/8" (213mm)	1.58 lb.

