

## DESCRIPTION

Designed for sloped ceiling installations for ceilings from 2/12 to 6/12 pitch. The socket aiming mechanism allows the lamp to be aimed straight down regardless of ceiling pitch.

Catalog #	Type
Project	
Comments	
Prepared by	Date

## SPECIFICATION FEATURES

### A...Baffle

One piece seamless baffle presents a clean finished appearance.

### B...Trim Ring

White polycarbonate Trim Ring.

### C...Housing

Telescoping housing for ceiling construction down to 2"x 8". With deeper ceilings the housing provides sharper cutoff.

### D...Junction Box

Junction box is listed for through branch circuit wiring and has six 1/2" knockouts with true pry-out slots.

### E...GOT NAIL! Pass-N-Thru™ Bar Hangers

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered

lumber and laminated beams

- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary.
- Automatic levelling flange aligns the housing and lets you hold the housing in place with one hand while driving nails
- Housing can be positioned at any point within 24" joist span
- Score lines allow "toolless" shortening for 12" joists
- Bar hangers do not need to be removed from frame for shortening
- Integral T-bar clips snaps onto T-bars - no additional clips required

### F...Socket

Exclusive socket aiming mechanism swivels and rotates to properly align lamp. Slope indicator provides quick and consistent lamp settings (factory set for 3/12 slope).

### G...Integral Thermal Protector

Thermal protector guards against misuse of insulation materials.

### Labels


U.L. damp location, U.L. Feed Through, CSA Certified, IP rated.




## H47T

5 0 W 1 2 V M R 1 6  
7 5 W R 3 0  
9 0 W P A R 3 8  
1 0 0 W R 3 0  
7 5 , 1 0 0 W A 1 9  
1 5 0 W A 2 1

6" RECESSED  
INCANDESCENT  
DOWNLIGHT



### Top View



## TRIMS

## ORDERING INFORMATION

SAMPLE NUMBER: H47T498P

Complete unit consists of housing and trim.

Housing	Trims
<b>H47T</b>	
H47T= 6" Non IC Slope Ceiling Housing	<p><b>BAFFLES</b></p> <p><b>Coilex Baffle</b>  <b>90W PAR38</b>            498P=Black            498W=White            OD: 7 7/8" (200mm)</p> <p><b>Coilex Baffle with Reflector</b>  <b>100W A19, 150W A21</b>            496P=Black            496W=White            OD: 7 7/8" (200mm)</p> <p><b>ADJUSTABLES</b></p> <p><b>Coilex Baffle Eyeball</b>  <b>75W R30</b>            417P=Black            417PB=Polished Brass            417W=White            OD: 8" (203mm)</p> <p><b>Eyeball-30° Tilt</b>  <b>100W R30</b>            78P=Satin White            78B=Brass            78PB=Polished Brass            78PAT=White Air-Tite            OD: 8" (203mm)</p> <p><b>Baffle Eyeball</b>  <b>50W 12V MR16</b>            1417P=Black Baffle, White Eyeball, White Trim Ring            1417W=White Baffle, White Eyeball, White Trim Ring            OD: 8" (203mm)</p>

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at [www.cooperlighting.com](http://www.cooperlighting.com)