

PHILIPS

Ceiling light

Functional

Surface Mount ceiling light

Warm White

12W, Round

8718696167823



Comfortable light with a slimmer fit

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 30,000 hours

Highlights

Suitable for low ceilings Slim design Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Plastic

Durability

- Lumen maintenance factor: 70%

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 5
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights

Other characteristics

- Lamp current: 280 mA
- Efficacy: 77 lm/W

Power consumption

- Voltage: 220-240 V

Product dimensions and weight

- Height: 3 cm
- Length: 16.4 cm
- Width: 16.4 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 164 mm
- Total lumen output fixture: 900
- Light color: 2700
- Mains power: 220
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC – product: 8718696167823
- Net weight: 0.29 kg
- Gross weight: 0.39 kg
- Height: 198 mm
- Length: 41 mm
- Width: 198 mm
- Material number (12NC):
915005625401



Issue date: 2024-02-02
Version: 0.84

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com