

PHILIPS


Ceiling light

Functional


CL800

brown

Dim



8718696173831



Set your desired ambience at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, the Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment.

Easy to experience

- Hassle-free installation that does not require wiring.

Light effect

- Uniform light distribution

Premium quality

- EyeComfort – light that's easy on the eyes

Control

- Tunable colour temperature
- Dimmable
- 4 pre-set scenes
- A remote control provides easy control for the light settings at up to 10 metres

Durability

- Long life span up to 15,000 hours

Highlights

Easy installation

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable colour temperature

Shift from crisp white light for focus to a warm yellow light for relaxation.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light to a cosy glow – just like traditional lamps.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

A remote control provides easy control for the light settings at up to 10 metres

Turn lights on or off or change brightness and colour from up to 10 metres away with this remote control.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Colour: brown
- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes
- Centrepiece: Yes

Light characteristics

- Colour rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living Room and Bedroom
- Type: Ceiling light

Product dimensions and weight

- Height: 9 cm
- Length: 55 cm
- Net weight: 3.7 kg
- Width: 55 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 4300
- Light colour: 2700-6500
- Mains power: 220-240
- Fixture dimmable: Yes
- LED: Yes
- Built-in LED: Yes
- Wattage bulb included: 32
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8718696173831
- Net weight: 3.700 kg
- Gross weight: 5.030 kg
- Height: 58.000 cm
- Length: 58.000 cm
- Width: 12.500 cm
- Material number (12NC): 915005810201



Issue date: 2021-09-13
Version: 0.389

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com