

# PHILIPS

## Ceiling light

Functional

Surface Mount ceiling light

Cool Day light

3W, Square

8718696769645



## Comfortable LED Ceiling light that's easy on your eyes

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

### Light effect

- Bright and even light

### Premium quality

- Durable and impact resistant die-cast aluminum housing
- EyeComfort - light that's easy on the eyes

### Durability

- Long life span up to 30,000 hours

# Highlights

## Bright and even light

Light is clear and distributed evenly around your space in a dependable manner.

## Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver

comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

## Design and finishing

- Color: White
- Material: plastic

## Durability

- Lumen maintenance factor: 0.7

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 5
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Functional

## Other characteristics

- Lamp current: 250 mA
- Efficacy: 63 lm/W

## Packaging dimensions and weight

- Net weight: 0.149 kg

## Power consumption

- Voltage: 220-240 V

## Product dimensions & weight

- Height: 3.5 cm
- Length: 9 cm
- Width: 9 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 190
- Light color: 6500
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 3
- IP code: IP20

## Packaging dimensions and weight

- EAN/UPC - product: 8718696769645
- Gross weight: 0.150 g
- Height: 4.000
- Length: 10.000
- Width: 10.000
- Material number (12NC): 919215850578



Issue date: 2023-11-08  
Version: 0.79

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)