

# PHILIPS

Bulb

LED

10W-83 (83W GLS, 16W CFLi)W

E27

Cool Daylight

8718696823767



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### **Choose for a sustainable solution**

- You can trust what the Philips packaging is saying.
- Contains no mercury

### **High quality LED light that lasts for decades**

- Designed for the comfort of your eyes

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 11 cm
- Weight: 0.04 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1020 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 965 | CCT of 6500K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 85 mA
- Efficacy: 102 lm/W

## Packaging information

- EAN: 8718696823767
- EOC: 871869682376700
- Product title: LEDBulb 10W E27 6500K 230V 2CT/6 9 APR

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 10 W
- Wattage equivalent: 83 W

## Product dimensions & weight

- Length: 11 cm

## Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1020 lumen
- Rated power: 10 W

## Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696823767
- Net weight: 0.070 kg
- Gross weight: 0.095 kg
- Height: 10.800 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC): 929003007957



Issue date: 2022-06-30  
Version: 0.28

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)