

PHILIPS

Bulb

LED

3W-25(GLS 25,CLFi 5)W

E27

Cool Daylight

8718699658106



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Instant on

High quality LED light that lasts for decades

- Light that shows true colors

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Instant on Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 8.7 cm
- Weight: 0.022 kg
- Width: 4.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 250 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 965 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 30 mA
- Efficacy: 83 lm/W

Packaging information

- EAN: 8718699658106
- EOC: 871869965810600
- Product title: LEDBulb 3W E27 6500K 230V P45 9 APR

Power consumption

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 3 W
- Wattage equivalent: 25 W

Product dimensions & weight

- Length: 8.7 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 250 lumen
- Rated power: 3 W

Technical specifications

- Frequency: 50–60 Hz

Bulb characteristics

- EAN/UPC – product: 8718699658106
- Rated beam angle: 150 degree(s)
- Height: 8.7 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 150 degree(s)
- Lamp current: 30 mA
- Net weight: 0.021 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.022 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.029 kg
- EAN: 8718699658106
- Rated luminous flux: 250 lumen
- Lamp shape: Non directional luster
- Width: 4.5 cm
- Color rendering index (CRI): 90
- Height: 8.750 cm
- EOC: 871869965810600
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 6500 K
- EyeComfort: Yes
- Length: 4.650 cm
- Product title: LEDBulb 3W E27 6500K 230V P45 9 APR
- Power factor: 0.41
- Rated power: 3 W
- Technology: LED
- Light Color Category: Cool Daylight
- Width: 4.650 cm
- Voltage: 220–240 V
- Type of glass: Frosted
- Nominal luminous flux: 250 lumen
- Material number (12NC): 929002973707
- Wattage: 3 W
- Length: 8.7 cm
- Starting time: <0.5 s
- Wattage equivalent: 25 W
- Warm-up time to 60% light: Instant full light
- Color Code: 965 | CCT of 6500K
- Frequency: 50–60 Hz



Issue date: 2022-06-12
Version: 0.44

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com