

# PHILIPS

Bulb (Dimmable)

LED

6.5W (35W)

E27

Warm White

Dimming



8718699666583



## State-of-the-art LED for the home

Sleek and bold, the new Philips deco LED giant modern collection provides a clean and minimalistic lighting experience that accentuates your home interiors.

### High quality light

- Cool, energizing light

### Create the right light for your home

- Perfect for general room lighting

### Light beyond illumination

- Dimmable

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

## Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Crystal
- Socket: E27
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 36.7 cm
- Weight: 0.6 kg
- Width: 9.4 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 400 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 38 mA
- Efficacy: 61 lm/W

## Packaging information

- EAN: 8718699666583
- EOC: 871869966658300
- Product title: LED Crystal\_giant 35W E27 smoky DIM

## Power consumption

- Power factor: 0.75
- Voltage: 220–240 V
- Wattage: 6.5 W
- Wattage equivalent: 35 W

## Product dimensions & weight

- Length: 36.7 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 400 lumen
- Rated power: 6.5 W

## Technical specifications

- Frequency: 50–60 Hz

8718699666583

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699666583
- Net weight: 0.494 kg
- Gross weight: 0.754 kg
- Height: 42.000 cm
- Length: 14.500 cm
- Width: 14.500 cm
- Material number (12NC): 929002094401



Issue date: 2023-11-08  
Version: 0.431

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)