

PHILIPS

Bulb

LED

4W-32(GLS 32, CLFi 7)W

E14

Cool Daylight

8718699704063



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Instant on

High quality LED light that lasts for decades

- Light that shows true colors

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Instant on Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 8.8 cm
- Weight: 0.02 kg
- Width: 4.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 350 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 965 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 35 mA
- Efficacy: 87 lm/W

Packaging information

- EAN: 8718699704063
- EOC: 871869970406300
- Product title: LEDBulb 4W E14 965 P45 AU

Power consumption

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 4 W
- Wattage equivalent: 32 W

Product dimensions & weight

- Length: 8.8 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 350 lumen
- Rated power: 4 W

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699704063
- Net weight: 0.033 kg
- Gross weight: 0.043 kg
- Height: 11.600 cm
- Length: 4.600 cm
- Width: 4.600 cm
- Material number (12NC):
929002975169



Issue date: 2023-01-06
Version: 0.92

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com