

PHILIPS

Bulb

LED

6W-55 (55W GLS, 10W CFLi)W

E27

Cool Daylight

8718699705459



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11 cm
- Weight: 0.03 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 580 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 965 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 55 mA
- Efficacy: 96 lm/W

Packaging information

- EAN: 8718699705459
- EOC: 871869970545900
- Product title: LEDBulb 6W E27 6500K 230V 2CT/6 9 APR

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 6 W
- Wattage equivalent: 55 W

Product dimensions & weight

- Length: 11 cm

Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 580 lumen
- Rated power: 6 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- EAN/UPC - product: 8718699705459
- Rated beam angle: 200 degree(s)
- Height: 11 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 200 degree(s)
- Lamp current: 55 mA
- Net weight: 0.070 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.03 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.095 kg
- EAN: 8718699705459
- Rated luminous flux: 580 lumen
- Lamp shape: Non directional bulb
- Width: 6 cm
- Color rendering index (CRI): 90
- Height: 10.800 cm
- EOC: 871869970545900
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 6500 K
- EyeComfort: Yes
- Length: 6.200 cm
- Product title: LEDBulb 6W E27 6500K
230V 2CT/6 9 APR
- Power factor: 0.5
- Rated power: 6 W
- Technology: LED
- Light Color Category: Cool Daylight
- Width: 10.000 cm
- Voltage: 220-240 V
- Type of glass: Frosted
- Nominal luminous flux: 580 lumen
- Material number (12NC):
929003006757
- Wattage: 6 W
- Length: 11 cm
- Starting time: <0.5 s
- Wattage equivalent: 55 W
- Warm-up time to 60% light: Instant
full light
- Color Code: 965 | CCT of 6500K
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.32

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com