

# PHILIPS

Bulb (Dimmable)

LED


8W-50W

E27

Warm White

Dimming

8718699729219



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Amber light

### Designed to be seen, looks good on and off

- Vintage style LED

# Highlights

## 2000K

This bulb has a color temperature of 2000K, providing you with an extra warm and intimate atmosphere. Ideal for home lighting design.

## Vintage (2000K & 2200K)

Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional color and amber glow of

old-fashioned incandescent lighting. The clear amber tinted glass bulb, brass finish base, and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cozy and warm ambience.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Amber

## Bulb dimensions

- Height: 14 cm
- Width: 6.4 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Light Color Category: Warm White
- Nominal luminous flux: 630 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 822 | CCT of 2200K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 52 mA
- Efficacy: 78 lm/W

## Packaging information

- EAN: 8718699729219
- EOC: 871869972921900
- Product title: LED classic 8-50W ST64 E27 820 GOLD D1PF

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A+

## Product dimensions & weight

- Length: 14 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 630 lumen
- Rated power: 8 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718699729219
- Net weight: 0.014 kg
- Gross weight: 0.032 kg
- Height: 12.600 cm
- Length: 5.500 cm
- Width: 5.500 cm
- Material number (12NC): 929001895949



Issue date: 2023-11-08  
Version: 0.32

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)