

# PHILIPS

Bulb

LED

6W-55 (55W GLS, 10W CFLi)W

E27

Cool White

8718699734589



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury

### Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27

## Bulb dimensions

- Height: 11 cm
- Width: 6 cm

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 4000 K
- Nominal luminous flux: 580 lm
- Warm-up time to 60% light: instant full light
- Color Code: 940 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 96 lm/W

## Packaging information

- EAN: 8718699734589
- EOC: 871869973458900
- Product title: LEDBulb 6W E27 4000K 230V 1CT/12 9 ID

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 6 W
- Wattage equivalent: 55 W

## Product dimensions and weight

- Length: 11 cm

## Technical specifications

- Frequency: 50-60 Hz



Issue date: 2024-01-20  
Version: 0.32

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)