

PHILIPS

Bulb

Clear

E14

8718699754693



Appliance Oven Tubular

Reliable operation when used in special lampholders at high oven temperatures (up to 300°C). Application in electrical and standard ovens, rotisseries and similar places subject to high operating temperatures.

Special purpose lighting

- For use in ovens

Highlights

For use in ovens



This Philips appliance bulb is specifically designed for use in ovens, resisting high heat up to 300 degrees Celcius.

Specifications

Bulb characteristics

- Socket: E14
- Lamp shape code: T25

Durability

- Average life (at 2.7 hrs/day): 1 year(s)
- Nominal lifetime: 1,000 h

Light characteristics

- Application: Special application, General light
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Nominal luminous flux: 172 lm
- Starting time: 0.0 s

Luminaire fit

- Shape: Tubular

Power consumption

- Voltage: 230 – 240 V
- Wattage: 25 W

Technical specifications

- Lamp holder: E14
- Number of lamps: 2

Packaging dimensions & weight

- EAN/UPC – product: 8718699754693
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 6 cm
- Length: 2.6 cm
- Width: 5.2 cm
- Material number (12NC): 924198244410



Issue date: 2024-02-02
Version: 0.16

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com