

PHILIPS

Dive Recessed Light
5.5W

Functional

DIVE SL261

Nickel

Dim



8718699755744



Create the perfect ambience with high quality dimmable light.

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cozy tones.

Match your interior

- Decorative metallic finishing

Light effect

- Bright and focused beam

Safety

- Moisture resistance

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Dimmable

Durability

- Long life span up to 15,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a

decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Nickel
- Material: Metal, Plastic

Durability

- Number of switch cycles: 10,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 31 mA
- Efficacy: 58 lm/W

Product dimensions and weight

- Net weight: 0.114 kg
- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Height: 5.5 cm
- Length: 8.5 cm
- Recessed distance: 1.5 cm
- Width: 8.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 85 mm
- Total lumen output fixture: 350
- Light color: 2700
- Mains power: AC 220–240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 5.5
- IP code: IP65/IP20
- Class of protection: Class II

8718699755744

Packaging dimensions and weight

- EAN/UPC - product: 8718699755744
- Net weight: 0.11 kg
- Gross weight: 0.14 kg
- Height: 9 cm
- Length: 7.5 cm
- Width: 10.5 cm
- Material number (12NC): 929002374520



Issue date: 2024-02-09
Version: 0.145

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com