

# PHILIPS

Bulb

LED

4.3W-40W

E27

Warm White



8718699761998



## Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer.

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### Create the right light for your home

- Perfect for general room lighting

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 10.6 cm
- Weight: 0.033 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Efficacy: 109 lm/W

## Packaging information

- EAN: 8718699761998
- EOC: 871869976199800
- Product title: LED classic 40W A60 E27 WW CL ND RFSRT4

**Power consumption**

- Power factor: 0.41
- Voltage: 220–240 V
- Wattage: 4.3 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): F

**Product dimensions & weight**

- Length: 10.6 cm

**Rated values**

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 470 lumen
- Rated power: 4.3 W

**Technical specifications**

- Frequency: 50–60 Hz

**The bulb**

- Color consistency: 6

**Bulb characteristics**

- EAN/UPC – product: 8718699761998
- Height: 10.6 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Lamp current: 40 mA
- Net weight: 0.060 kg
- Rated lifetime: 15,000 hour(s)
- Color consistency: 6
- Intended use: Indoor
- Weight: 0.033 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.098 kg
- EAN: 8718699761998
- Rated luminous flux: 470 lumen
- Lamp shape: Non directional bulb
- Width: 6 cm
- Color rendering index (CRI): 80
- Height: 14.600 cm
- EOC: 871869976199800
- Socket: E27
- Number of switch cycles: 20,000
- Color temperature: 2700 K
- EyeComfort: Yes
- Length: 6.500 cm
- Product title: LED classic 40W A60 E27 WW CL ND RFSRT4
- Power factor: 0.41
- Rated power: 4.3 W
- Technology: LED
- Light Color Category: Warm White
- Width: 6.300 cm
- Voltage: 220–240 V
- Type of glass: Clear
- Nominal luminous flux: 470 lumen
- Material number (12NC): 929001890055
- Wattage: 4.3 W
- Length: 10.6 cm
- Starting time: <0.5 s
- Wattage equivalent: 40 W
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K
- Frequency: 50–60 Hz



Issue date: 2022-06-27  
Version: 0.249

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)