

PHILIPS

Bulb

LED

8.5W-75W

E27

Warm White



8718699762995



Warm white light, no compromise on light quality

Familiar shapes you know and love. They use around 85% less energy than traditional light bulbs thanks to the latest LED energy-saving technology and last ten times longer.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Create the right light for your home

- Perfect for general room lighting

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 10.4 cm
- Weight: 0.036 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 1055 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA
- Efficacy: 124 lm/W

Packaging information

- EAN: 8718699762995
- EOC: 871869976299500
- Product title: LED classic 75W E27 WW A60 CL ND RFSRT4

Power consumption

- Power factor: 0.52
- Voltage: 220–240 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W
- Energy Efficiency Label (EEL): E

Product dimensions & weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1055 lumen
- Rated power: 8.5 W

Technical specifications

- Frequency: 50–60 Hz

The bulb

- Color consistency: 6

Packaging dimensions and weight

- EAN/UPC - product: 8718699762995
- Net weight: 0.060 kg
- Gross weight: 0.098 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 6.300 cm
- Material number (12NC):
929002025455



Issue date: 2022-01-18
Version: 0.219

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com