

PHILIPS

Bulb (Dimmable)

LED

5.5W-25W

E27

Flame

Dimming



8718699774837



A light bulb like no other

Philips LED flame candles provide a beautiful, warm light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dims to a warm glow

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Transparent Amber

Bulb dimensions

- Height: 10.4 cm
- Weight: 0.035 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Flame
- Nominal luminous flux: 250 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 820 | CCT of 2000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 35 mA
- Efficacy: 45 lm/W

Packaging information

- EAN: 8718699774837
- EOC: 871869977483700
- Product title: LED classic 25W A60 E27GOLD SP D RF SRT4

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 5.5 W
- Wattage equivalent: 25 W

Product dimensions & weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 250 lumen
- Rated power: 5.5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699774837
- Net weight: 0.030 kg
- Gross weight: 0.054 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 6.300 cm
- Material number (12NC): 929002223855



Issue date: 2023-11-08
Version: 0.218

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com