

PHILIPS

4 inch recessed
downlight 9W


Smart LED

Tunable white

Cut out Ø102-110MM

IP20/Round/White

8718699789978



Easy-to-use smart tunable white downlight

Enjoy convenience in everyday life with smart Wi-Fi LED lighting. This downlight gives warm white to cool daylight for cozy moments and functional tasks. Control instantly via app or voice and create your desired ambiance. Works with WiZ.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules
- Preset wellbeing features
- Energy monitoring

Light modes

- Tunable warm to cool white and preset modes
- Customize Scenes with preset dynamic light modes

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules



Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Preset wellbeing features



Use the preset wellbeing features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm through the day. WiZ will provides you bright daylight when you need to get energized and focus, and transition smoothly to soft warm white to help you relax and sleep better.

Energy monitoring



The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

Tunable warm to cool white and preset modes



Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Customized Scenes



Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, remote or voice.

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: 90 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Power consumption

- Voltage: 220–240 V

Product dimensions & weight

- Cut out length: 10.5 cm
- Cut out width: 10.5 cm
- Height: 4.7 cm
- Length: 12 cm
- Net weight: 0.091 kg
- Recessed distance: 10.1 cm
- Width: 12 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 120 mm
- Total lumen output fixture: 600
- Light color: 2700–6500
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II

Design and finishing

- Color: white
- Especially designed for: Functional
- EAN/UPC – product: 8718699789978
- Warranty: 3 year(s)
- Beam angle: 90 degree(s)
- Net weight: 0.091 kg
- Cut out length: 10.5 cm
- Material: plastic
- Gross weight: 0.117 kg
- Cut out width: 10.5 cm
- Adjustable spot head: No
- Color rendering index (CRI): 80
- Height: 12.200 cm
- Height: 4.7 cm
- Lifetime up to: 15,000 hour(s)
- Length: 5.500 cm
- Width: 12.200 cm
- Voltage: 220–240 V
- Material number (12NC): 929002532407
- Length: 12 cm
- Net weight: 0.091 kg
- Recessed distance: 10.1 cm
- Width: 12 cm
- Diameter: 120 mm
- Dimmable with remote control: Yes
- Total lumen output fixture: 600
- Light color: 2700–6500
- LED integrated: Yes
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II
- Remote control included: No
- Centerpiece: Yes



Issue date: 2023-11-08
Version: 0.44

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com