

PHILIPS

Spot (Dimmable)

LED

8W-50W

GU5.3

Cool White

Dimming

8719514274136



Durable LED accent lighting with a focused bright beam

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

High quality light

- Cool, white light

Choose for a sustainable solution

- Saves up to 80% Energy

Create the right light for your home

- Perfect for accent lighting and general purpose lighting

Highlights

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

60° beam - spot



Modern lighting with a familiar extra wide angle light output (60 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

Bulb dimensions

- Height: 5 cm
- Weight: 0.05 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 670 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 1000 mA
- Efficacy: 83 lm/W

Packaging information

- EAN: 8719514274136
- EOC: 871951427413600
- Product title: LED 8-50W MR16 60D 840 DIM 1PF/10

Power consumption

- Power factor: 0.7
- Voltage: 12 V
- Wattage: 8 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight

- Length: 5 cm

Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 25,000 h
- Rated luminous flux: 670 lumen
- Rated peak intensity: 600 cd
- Rated power: 8 W

Technical specifications

- Frequency: 50 Hz



Issue date: 2023-11-07
Version: 0.24

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com