

# PHILIPS

Bulb

LED

7.5W-60(60W GLS, 12W CFL)W

E27

White

8719514275171



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

**Light beyond illumination**

- 3 hours of emergency lighting

# Highlights

## 3 hours of emergency lighting

You can rely on this emergency bulb for 3 hours of battery powered light.

Ideal for power outages and is automatically recharged from the mains when switched on.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 13.75 cm
- Weight: 0.108 kg
- Width: 7.1 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 700 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 55mA-120 mA
- Efficacy: 93 lm/W

## Packaging information

- EAN: 8719514275171
- EOC: 871951427517100
- Product title: LEDBulb BB7.5-60W E27 3000K 110-240V A67

## Power consumption

- Power factor: 0.51
- Voltage: 110-240 V
- Wattage: 7.5 W
- Wattage equivalent: 60 W

## Product dimensions & weight

- Length: 13.75 cm

## Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 700 lumen
- Rated power: 7.5 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8719514275171
- Net weight: 0.128 kg
- Gross weight: 0.150 g
- Height: 13.750
- Length: 7.000
- Width: 7.000
- Material number (12NC): 929002454907



Issue date: 2023-11-08  
Version: 0.183

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)