

# PHILIPS

Bulb

LED

11W-95(95W GLS, 20W CFL)W

E27

Cool Daylight

8719514286443



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### **Choose for a sustainable solution**

- You can trust what the Philips packaging is saying.
- Contains no mercury

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no

ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.8 cm
- Weight: 0.036 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 8 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 8,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1250 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 95 mA
- Efficacy: 113 lm/W

## Packaging information

- EAN: 8719514286443
- EOC: 871951428644300
- Product title: ESS LEDBulb 11W E27 6500K 230V 4CT/3 ID

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 11 W
- Wattage equivalent: 95 W

## Product dimensions & weight

- Length: 10.8 cm

## Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 8,000 hour(s)
- Rated luminous flux: 1250 lumen
- Rated peak intensity: 248 cd
- Rated power: 11 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514286443
- Net weight: 0.280 kg
- Gross weight: 0.336 kg
- Height: 11.900 cm
- Length: 6.200 cm
- Width: 24.900 cm
- Material number (12NC): 929002299898



Issue date: 2022-07-19  
Version: 0.21

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)