

PHILIPS

Starter kit: 3 E27 smart bulbs (1100) + dimmer switch

Hue White Ambiance

Up to 1100 lumens*

Warm-to-cool white light

Hue Bridge included

Dimmer switch included



8719514291232



Easy smart lighting


Enjoy relaxing and energising scenes or create your own routines right out of the box with the Hue White ambiance E27 starter kit. Includes Hue Bridge, three smart bulbs that offer the full spectrum of white light and a dimmer switch.

Limitless possibilities

- Control with your voice
- Get in the mood with warm to cool white smart lights
- Away-from-home smart light control
- Enjoy the right smart lighting for daily tasks
- Smart home automation hub: Hue Bridge
- Control lights instantly
- Easy, wireless installation

Highlights

Control with your voice



Philips Hue works with Amazon Alexa, Apple HomeKit and Google Home, powered by the Google Assistant, to allow you to control your lights with your voice. Turn your lights on and off. Dim to the desired brightness for a perfect ambiance. Even recall pre-set scenes, change colours and more – all without lifting a finger.

Get in the mood



Use over 50,000 shades of warm to cool white light to put you in the mood to work, play, or relax — no matter what time of day it is. Start your morning off on the right foot with cool, energising bright white light, or settle down for the night with golden tones.

Control lights away from home



The Philips Hue app gives you complete control over your lights, even if you're not at home. Switch your lights off and on remotely using just the app to ensure your home is always lit the way you want it.

Smart lighting for daily tasks



Make your day easier with four preset light scenes that have been handcrafted for your daily tasks. Two cool-toned scenes, Energise and Concentrate, help you get going in the morning and keep your focus, while the warmer scenes of Read and Relax help you enjoy a good book and a rested mind.

The Hue Bridge



The Hue Bridge is an essential component to a personal Philips Hue smart lighting system. It is the brains of the operation, communicating with both your smart light lamps and the Hue app to ensure that everything works together. It also enables smart home automation features like scheduling routines and timers.

Control lights instantly



Get instant control over your Philips Hue smart lights with the Hue dimmer switch. With the touch of a button, your entire household can instantly dim or brighten the room, turn lights on and off, or set light scenes.

Easy, wireless installation

The battery-powered, wireless design of the Hue dimmer switch lets you mount it anywhere with the included adhesive tape. Remove the switch from its wall plate and use it as a remote control or attach it to any magnetic surface.

Specifications

Lamp dimensions

- Dimensions (WxHxD): 60x110

Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Dimmable with the Hue app and switches: Yes

Guarantee

- 2 years: Yes

Packaging information

- EAN: 8719514291232

Power consumption

- Energy efficiency label (EEL): F

Service

- Warranty: 2 year(s)

Technical specifications

- Lumen output at 4000K: 1,055 lm
- Weight: 72
- Bulb technology: LED
- Fitting/cap: E27
- EPREL registration number: 1522881

The Bridge

- Frequency band: 2400-2483.5 MHz
- Height: 26 mm
- Length X Width: 88 x 88 mm
- Max. number of accessories: 12
- Max. number of bulbs: 50
- Mounting options: Desktop, Wall
- Power adapter: 100-240 V AC / 50-60 Hz
- Power consumption: 250mA max

The bulb

- Reference Control Setting*: 4000K; via Hue app scene "Cool bright"
- Colour temperature: 2200-6500K + 16 million colors
- Diameter: 60 mm
- Form factor: A60
- Height: 109 mm
- Input voltage: 220V-240V
- Lifetime: 25,000 h
- Light output: Warm to cool white light
- Lumen output: 1055 lm @ 4000K
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: 0.5
- Rated lifetime: 25,000 h
- Software upgradable: Yes
- Start up: Instant 100% light output
- Wattage: 11 W
- Communication protocol: Bluetooth and Zigbee
- Software upgradable: When connected to Bluetooth app or Hue Bridge

The switch

- Batteries included: 1 x CR2032
- Frequency band: 2400-2483,5 MHz
- IP rating: 20
- Lifetime: 50.000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 2 year(s)
- Mounting options: wall, freestanding
- Special features: Not applicable
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Wall plate depth: 6 mm
- Wall plate height: 76 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g
- Weight of switch: 37 g

What's in the box

- Bridge: 1
- Ethernet network cable: 1
- Hue bulbs: 3
- Hue dimmer switch: 1
- Power adapter: 1

What's supported

- Compatible with Effects feature: Yes
- HomeKit compatible: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above
- Voice assistants: Amazon Alexa, Google Assistant, Apple HomeKit (Via Hue Bridge), Microsoft Cortana (Via Hue Bridge)

Packaging dimensions and weight

- EAN/UPC – product: 8719514291232
- Net weight: 0.55 kg
- Gross weight: 1.01 kg
- Height: 14 cm
- Length: 17.6 cm
- Width: 21.9 cm
- Material number (12NC): 929002468403



Issue date: 2024-02-04
Version: 0.525

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com