

PHILIPS


Doorbell Chime

Other Wiring Devices

LeafStyle

Metallica

8719514298132



High quality switch and socket designed to safely last for years

Philips LeafStyle provides modern design, high safety standard and easy to install switch & socket to your family.

Convenience

- Strong sound output

Safety and Durability

- High quality PC
- Safety and Durability

Highlights

Strong sound output

Better sound output around 100dB.

High quality PC

High quality PC for Cover and Base.

Safety and Durability

1. High quality PC for Cover and Base.
2. Key metal parts are used with 0.6mm thickness phosphor bronze.
3. Pass IEC standard and follow more strict Philips internal design rule.

Specifications

Design and finishing

- Color: White
- Material: PC

Durability

- Number of Operation Cycles: 10,000

Power consumption

- Voltage: 220 V

Product dimensions and weight

- Height: 4.2 cm
- Length: 9.9 cm
- Width: 16.4 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8719514298132
- Net weight: 0.3 kg
- Gross weight: 0.34 kg
- Height: 4.2 cm
- Length: 9.9 cm
- Width: 16.4 cm
- Material number (12NC): 913713877601



Issue date: 2024-02-02
Version: 0.261

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com