

PHILIPS

ST64 – E27 smart
bulb

Hue White Ambiance
Filament

Warm to cool white

Instant control via Bluetooth

Control with app or voice*

Add Hue Bridge to unlock more



8719514301467



Easy smart lighting

Get that vintage look with all the benefits of a smart bulb with the ST64 bulb, an Edison-style LED bulb that features a coiled inner filament and dimmable warm-to-cool white light.

Limitless possibilities

- Vintage design meets modern capabilities

Easy smart lighting

- Control up to 10 lights with the Bluetooth app
- Control lights with your voice*
- Set the right mood with soft white light



Highlights

Vintage design meets modern capabilities



Capture the popular look of Edison bulbs, featuring a distinct glowing inner coil and transparent globe, with smart filament bulbs. These smart retro-style LED bulbs combine the look and feel of simple vintage design with the power of Philips Hue smart lighting.

Control up to 10 lights with the Bluetooth app



With the Hue Bluetooth app, you can control your Hue smart lights in a single room of your home. Add up to 10 smart lights and control them all with just the touch of a button on your mobile device.

Control lights with your voice*



Get hands-free control of your lights and use your voice instead! Simple voice commands allow you to control multiple lights in a room or just a single lamp. *Works with the Google Assistant and Amazon Alexa.

Set the right mood with soft white light



Hue bulbs and light fixtures use a soft white light. Dimmable from bright daylight to low nightlights, these smart lights allow you to fill your home with just the right level of warm light when you need it.

Specifications

Lamp dimensions

- Dimensions (WxHxD): 60x133

Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Dimmable with the Hue app and switches: Yes

Guarantee

- 2 years: Yes

Power consumption

- Energy efficiency label (EEL): G

Service

- Warranty: 2 year(s)

Technical specifications

- Lumen output at 4000K: 550 lm
- Weight: 56
- Bulb technology: LED
- Fitting/cap: E27
- Lumen output at 2700K: 550 lm
- EPREL registration number: 400276

The bulb

- Colour temperature: 2200-4500K
- Diameter: 60 mm
- Form factor: ST64
- Height: 133 mm
- Input voltage: 220V-240V
- Lifetime: 15,000 h
- Light output: Warm to cool white light
- Lumen output: 550 lm
- Max. operation power: 7 W
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: 0.6
- Rated lifetime: 15,000 h
- Software upgradable: when connected to the Bluetooth app or Hue Bridge
- Start up: Instant 100% light output
- Wattage: 7 W
- Communication protocol: Bluetooth and Zigbee
- Software upgradable: When connected to Bluetooth app or Hue Bridge

What's in the box

- Hue bulbs: 1

What's supported

- Compatible with Effects feature: Yes
- HomeKit compatible: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above
- Voice assistants: Amazon Alexa, Google Assistant, Apple HomeKit (Via Hue Bridge), Microsoft Cortana (Via Hue Bridge)

Packaging dimensions and weight

- EAN/UPC - product: 8719514301467
- Net weight: 0.05 kg
- Gross weight: 0.12 kg
- Height: 17.6 cm
- Length: 7.2 cm
- Width: 7.2 cm
- Material number (12NC): 929002477701



Issue date: 2024-02-02
Version: 0.328

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com