

PHILIPS

Spot

LED

4.8-3.5-1.5W-50W

GU10

2700-2500-2200



8719514307728



One lamp. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cozy warm glow. All you need is your existing switch.

High quality light

- Light all around

Light beyond illumination

- Restore the lamp to the default factory setting
- No dimmer or additional installation needed
- The lamp can memorize your last setting

Highlights

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronized, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorize your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favorite mode when you turn it on again.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

Bulb dimensions

- Height: 5.4 cm
- Weight: 0.048 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-2500-2700 K
- Light Color Category: Warm White/Flame
- Nominal luminous flux: 355 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827-825-822 | CCT of 2700K/2500K/2200K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA
- Efficacy: 73 lm/W

Packaging information

- EAN: 8719514307728
- EOC: 871951430772800
- Product title: LED SSW 50W GU10 WW 36D RF ND 2SRT6

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 4.8 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): F

Product dimensions & weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 36 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 355 lumen
- Rated peak intensity: 600 cd
- Rated power: 4.8–3.5–1.5 W

Technical specifications

- Frequency: 50–60 Hz

The bulb

- Color consistency: 6

Packaging dimensions and weight

- EAN/UPC – product: 8719514307728
- Net weight: 0.096 kg
- Gross weight: 0.119 kg
- Height: 12.700 cm
- Length: 5.300 cm
- Width: 8.500 cm
- Material number (12NC): 929002981818



Issue date: 2021-09-22
Version: 0.93

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com