

# PHILIPS

Bulb

LED

5.5W-40W

E27

Flame



8719514313866



## State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

### Easy-to-use smart lighting for a more convenient everyday life


- Dimmable extra warm white light

### Designed to be seen, looks good on and off

- Looks good on and off

# Highlights

## Dimmable extra warm white light



Enhance the ambiance in your home with extra warm white light that dims smoothly via app or voice to your desired brightness level.

## Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: E27
- Bulb Finish: Amber
- Bulb Material: Glass

## Bulb dimensions

- Height: 18.8 cm
- Width: 20.2 cm

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 1800 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 818 | CCT of 1800K
- Correlated Color Temperature (Nom): 1800 K
- Luminous Efficacy (rated) (Nom): 85 lm/W
- Luminous Flux: 470 lm
- Stroboscopic effect visibility measure (SVM): 0.4

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 85 lm/W
- CE mark: Yes
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514313866
- EOC: 871951431386600
- Product title: LEDClassic 40W Mushroom E27 1800K GOLD D

## Power

- Power Factor (Fraction): 0.7

## Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 5.5 W
- Wattage equivalent: 40 W
- Power Consumption: 5.5 W

## Product dimensions and weight

- Length: 18.8 cm

## Rated values

- Rated lifetime: 15,000 hour(s)

#### Technical specifications

- Frequency: 50-60 Hz
- Dimmable: Only with specific dimmers
- Flickering value (PstLM) - Flickering value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60 Hz
- Cap-Base: E27

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514313866
- Net weight: 0.24 kg
- Gross weight: 0.53 kg
- Height: 21.7 cm
- Length: 22.4 cm
- Width: 22.4 cm
- Material number (12NC): 929002984001



Issue date: 2024-02-02  
Version: 0.188

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)