

PHILIPS

Bulb (Dimmable)


LED

5.9W-60W

E27

Warm Glow

Dimming



8719514323834



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for general room lighting

Highlights

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 10.4 cm
- Weight: 0.03 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA
- Efficacy: 136 lm/W

Packaging information

- EAN: 8719514323834
- EOC: 871951432383400
- Product title: LED classic 60W A60 E27 CL WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 5.9 W
- Wattage equivalent: 60 W
- Energy Efficiency Label (EEL): D

Product dimensions and weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 806 lumen
- Rated power: 5.9 W

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1109131
- Flux measurement reference: Sphere

The bulb

- Color consistency: 6

8719514323834

Packaging dimensions and weight

- EAN/UPC - product: 8719514323834
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm
- Material number (12NC): 929003010301



Issue date: 2023-09-07
Version: 0.173

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com