

PHILIPS

Candle & Lustre
(Dimmable)

LED

3.4W-40W

E14

Warm Glow

Dimming



8719514324213



Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

Specifications

Characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non directional candle
- Socket: E14
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 9.7 cm
- Weight: 0.013 kg
- Width: 3.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 24 mA
- Efficacy: 138 lm/W

Packaging information

- EAN: 8719514324213
- EOC: 871951432421300
- Product title: LED classic 40W B35 E14 CL WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.4 W
- Wattage equivalent: 40 W
- Energy Efficiency Label (EEL): D

Product dimensions & weight

- Length: 9.7 cm

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 470 lumen
- Rated power: 3.4 W

Technical specifications

- Frequency: 50-60 Hz

The bulb

- Color consistency: 6

8719514324213

Packaging dimensions and weight

- EAN/UPC - product: 8719514324213
- Net weight: 0.014 kg
- Gross weight: 0.033 kg
- Height: 14.600 cm
- Length: 4.600 cm
- Width: 6.300 cm
- Material number (12NC): 929003012201



Issue date: 2021-09-23
Version: 0.186

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com