

PHILIPS

Filament Candle
Clear 40W P45 E14

LED

3.4W-40W

E14

Warm Glow

Dimming



8719514324398



Experience dimmable, warm white LED light

Philips LED clear lustres provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for decorative fixtures with small (E14) fittings.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Type of glass: Clear
- Lamp Finish: Clear
- Bulb material: Glass

Lamp dimensions

- Height: 8 cm
- Width: 4.5 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200–2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 138 lm/W

Packaging information

- EAN: 8719514324398
- EOC: 871951432439800
- Product title: LED classic 40W P45 E14 WGD90 CL SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220–240 V
- Wattage: 3.4 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): D

Product dimensions and weight

- Length: 8 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 1109144

The bulb

- Colour consistency: 6

Packaging dimensions and weight

- EAN/UPC – product: 8719514324398
- Net weight: 0.02 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm
- Material number (12NC): 929003013199



Issue date: 2024-02-02
Version: 0.251

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com