

# PHILIPS

Candle & Lustre

LED

5.5W-35W

B22

Warm White

8719514327382



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- No visible flicker

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 8.5 cm
- Weight: 0.038 kg
- Width: 4.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: poc
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 50 mA
- Efficacy: 85 lm/W

## Packaging information

- EAN: 8719514327382
- EOC: 871951432738200
- Product title: LED 5.5-35W B22 2700K P45 FR ND AU 1PF/6

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 5.5 W
- Wattage equivalent: 35 W

## Product dimensions & weight

- Length: 8.5 cm

## Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 470 lumen
- Rated power: 5.5 W

## Technical specifications

- Frequency: 50-60 Hz



Issue date: 2023-11-07  
Version: 0.33

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)