

PHILIPS

Bulb

LED

9.5W-75W

E27

Cool Daylight

8719514327481



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker
- Light all around

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11.43 cm
- Weight: 0.05 kg
- Width: 3.72 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1050 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 75 mA
- Efficacy: 110 lm/W

Packaging information

- EAN: 8719514327481
- EOC: 871951432748100
- Product title: LEDStick 9.5W E27 6500K 1PF/6 AU

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 9.5 W
- Wattage equivalent: 75 W

Product dimensions & weight

- Length: 11.43 cm

Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1050 lumen
- Rated power: 9.5 W

Technical specifications

- Frequency: 50–60 Hz

Bulb characteristics

- EAN/UPC - product: 8719514327481
- Rated beam angle: 200 degree(s)
- Height: 11.43 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 200 degree(s)
- Lamp current: 75 mA
- Net weight: 0.042 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.05 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.055 kg
- EAN: 8719514327481
- Rated luminous flux: 1050 lumen
- Lamp shape: Non directional bulb
- Width: 3.72 cm
- Color rendering index (CRI): 80
- Height: 14.700 cm
- EOC: 871951432748100
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 6500 K
- EyeComfort: Yes
- Length: 3.900 cm
- Product title: LEDStick 9.5W E27
6500K 1PF/6 AU
- Power factor: 0.51
- Rated power: 9.5 W
- Technology: LED
- Light Color Category: Cool Daylight
- Width: 3.900 cm
- Voltage: 220-240 V
- Type of glass: Frosted
- Nominal luminous flux: 1050 lumen
- Material number (12NC):
929001901676
- Wattage: 9.5 W
- Length: 11.43 cm
- Starting time: <0.5 s
- Wattage equivalent: 75 W
- Warm-up time to 60% light: Instant
full light
- Color Code: 865 | CCT of 6500K
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.39

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com