

# PHILIPS

Candle & Lustre

LED

1.7W-15W

E14

Warm White

8719514327580



## Perfect lamp for your household appliances

The Philips T25 LED bulb was specially designed to replace your current halogen or incandescent bulbs, and can be used in fridge or cooker hoods with small fittings.

### **Choose a simple replacement for your old bulbs**

- Perfect fit and high-quality finishing

### **Create the right light for your home**

- Perfect for general room lighting

### **Light beyond illumination**

- For use in refrigerators and freezers

# Highlights

## Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

## Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

## Special purpose appliance bulb

Philips refrigerator bulbs can be used in refrigerators, freezers, and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips refrigerator bulb for a long, useful life.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 5.9 cm
- Weight: 0.014 kg
- Width: 2.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 240 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 20 mA
- Efficacy: 88 lm/W

## Packaging information

- EAN: 8719514327580
- EOC: 871951432758000
- Product title: LED 15W T25 E14 WW FR ND 1CT/12

#### Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 1.7 W
- Wattage equivalent: 15 W

#### Product dimensions & weight

- Length: 5.9 cm

#### Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 150 lumen
- Rated power: 1.7 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions & weight

- EAN/UPC - product: 8719514327580
- Net weight: 0.012 kg
- Gross weight: 0.020 kg
- Height: 6.700 cm
- Length: 2.500 cm
- Width: 2.500 cm
- Material number (12NC):  
929001325776



Issue date: 2022-07-19  
Version: 0.33

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)