

# PHILIPS

Spot

LED

5W-50W

GU5.3

Warm White

8719514327627



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

### High quality light

- Bright white light

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambiance for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Type of glass: Clear
- Bulb Finish: Clear
- Bulb Material: Glass

## Bulb dimensions

- Height: 4.6 cm
- Width: 5.1 cm

## Design and finishing

- Material: Glass

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +40 °C

## Light characteristics

- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 390 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Efficacy (rated) (Nom): 78 lm/W
- Luminous Flux: 390 lm

## Other characteristics

- Efficacy: 78 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514327627
- EOC: 871951432762700
- Product title: LEDspots 5-50W MR16 830 60D 2pk

## Power

- Power Factor (Fraction): 0.6

#### Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

#### Product dimensions and weight

- Length: 4.6 cm

#### Rated values

- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 400 cd

#### Technical specifications

- Frequency: - Hz
- Dimmable: No
- Line Frequency: - Hz
- Cap-Base: GU5.3

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514327627
- Net weight: 0.08 kg
- Gross weight: 0.09 kg
- Height: 8.9 cm
- Length: 5.1 cm
- Width: 5.1 cm
- Material number (12NC):  
929001280476



Issue date: 2024-02-06  
Version: 0.29

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)