PHILIPS

Spot

LED

4.6W-50W

GU10

Warm White

8719514327665



Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

High quality light
- Bright white light

Choose for a sustainable solution
- Safe for any room and convenient to recycle

High quality LED light that lasts for decades
- Designed for the comfort of your eyes

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10

Bulb dimensions
- Height: 5.4 cm
- Width: 5 cm

Durability
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics
- Beam angle: 60 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 410 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Efficacy: 89 lm/W

Packaging information
- EAN: 8719514327665
- EOC: 871951432766500
- Product title: LEDspots 4.6-50W GU10 830 60D 2pk

Power consumption
- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W

Product dimensions and weight
- Length: 5.4 cm

Rated values
- Rated peak intensity: 450 cd

Technical specifications
- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8719514327665
- Net weight: 0.1 kg
- Gross weight: 0.12 kg
- Height: 10.6 cm
- Length: 5.1 cm
- Width: 5.1 cm
- Material number (12NC): 929001287676

Issue date: 2024-02-02
Version: 0.30

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com