

PHILIPS

Spot

LED

4.6W-50W

GU10

Warm White

8719514327764



Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

High quality light

- Bright white light

Choose for a sustainable solution

- Safe for any room and convenient to recycle

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambiance for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

Bulb dimensions

- Height: 5.4 cm
- Weight: 0.05 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 410 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 39 mA
- Efficacy: 89 lm/W

Packaging information

- EAN: 8719514327764
- EOC: 871951432776400
- Product title: LEDspots 4.6-50W GU10 830 60D 4pk

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W

Product dimensions & weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 410 lumen
- Rated peak intensity: 450 cd
- Rated power: 4.6 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- EAN/UPC - product: 8719514327764
- Rated beam angle: 60 degree(s)
- Height: 5.4 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 60 degree(s)
- Lamp current: 39 mA
- Net weight: 0.200 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.05 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.239 kg
- EAN: 8719514327764
- Rated luminous flux: 410 lumen
- Lamp shape: Directional reflector
- Width: 5 cm
- Color rendering index (CRI): 80
- Height: 12.400 cm
- EOC: 871951432776400
- Rated peak intensity: 450 cd
- Socket: GU10
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- EyeComfort: Yes
- Length: 5.100 cm
- Product title: LEDspots 4.6-50W
GU10 830 60D 4pk
- Power factor: 0.5
- Rated power: 4.6 W
- Technology: LED
- Light Color Category: Warm White
- Width: 10.500 cm
- Voltage: 220-240 V
- Nominal luminous flux: 410 lumen
- Material number (12NC):
929001287677
- Wattage: 4.6 W
- Length: 5.4 cm
- Starting time: 0.5 s
- Wattage equivalent: 50 W
- Warm-up time to 60% light: Instant
full light
- Color Code: 830 | CCT of 3000K
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.29

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com