

# PHILIPS

Bulb (Dimmable)

LED

10.5W-75W

B22

Warm White

Dimming

8719514333673



## Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- Dims to a warm glow
- Dimmable

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 11 cm
- Weight: 0.075 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 1055 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 927 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 55 mA
- Efficacy: 100 lm/W

## Packaging information

- EAN: 8719514333673
- EOC: 871951433367300
- Product title: LEDBulb 10.5-75WA60 B22 2700K FR D AU/NZ

#### Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W
- Energy Efficiency Label (EEL): A+

#### Product dimensions & weight

- Length: 11 cm

#### Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1055 lumen
- Rated power: 10.5 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions & weight

- EAN/UPC - product: 8719514333673
- Net weight: 0.050 kg
- Gross weight: 0.075 kg
- Height: 15.300 cm
- Length: 6.500 cm
- Width: 7.200 cm
- Material number (12NC):  
929002069479



Issue date: 2021-05-05  
Version: 0.138

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)