

PHILIPS

Bulb (Dimmable)

LED

13W-100W

B22

Warm White

Dimming

8719514333697



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Dimmable

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted
- Bulb Finish: Frosted

Bulb dimensions

- Height: 11 cm
- Weight: 0.075 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 1521 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 117 lm/W
- Luminous Flux: 1,521 lumen

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA
- Efficacy: 117 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514333697
- EOC: 871951433369700
- Product title: LEDBulb 13-100W B22 2700K D 1PF/6 AU

Power

- Power Factor (Fraction): 0.9

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage: 13 W
- Wattage equivalent: 100 W
- Power Consumption: 13 W

Product dimensions and weight

- Length: 11 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1521 lumen
- Rated power: 13 W

Technical specifications

- Frequency: 50–60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: B22 | B22

Packaging dimensions and weight

- EAN/UPC - product: 8719514333697
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC): 929002069619



Issue date: 2023-09-07
Version: 0.304

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com