

PHILIPS

Bulb (Dimmable)

LED

7W-60W

E27

Warm Glow

Dimming

8719514338760



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dims to a warm glow

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 10.6 cm
- Weight: 0.04 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 270 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700-2200 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 927-922 | CCT of 2700K-2200K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA
- Efficacy: 115 lm/W

Packaging information

- EAN: 8719514338760
- EOC: 871951433876000
- Product title: LED classic 7-60W A60 E27 CL WGD90

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W

Product dimensions & weight

- Length: 10.6 cm

Rated values

- Rated beam angle: 270 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 806 lumen
- Rated power: 7 W

Technical specifications

- Frequency: 50-60 Hz

8719514338760

Packaging dimensions and weight

- EAN/UPC - product: 8719514338760
- Net weight: 0.034 kg
- Gross weight: 0.056 kg
- Height: 15.000 cm
- Length: 6.600 cm
- Width: 6.600 cm
- Material number (12NC): 929002391749



Issue date: 2021-11-26
Version: 0.38

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com