

# PHILIPS

Bulb (Dimmable)

LED


7W-60W

E27

Warm Glow

Dimming

8719514338821



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Designed for the comfort of your eyes

### Light beyond illumination

- Dims to a warm glow

### Designed to be seen, looks good on and off

- Classic glass LED

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

## Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Clear
- Bulb Finish: Clear

## Bulb dimensions

- Height: 14.3 cm
- Width: 6.4 cm

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 270 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700-2200 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: instant full light
- Color Code: 927-922 | CCT of 2700K-2200K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 115 lm/W

## Packaging information

- EAN: 8719514338821
- EOC: 871951433882100
- Product title: LED classic 7-60W ST64 E27 CL WGD90

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W

## Product dimensions and weight

- Length: 14.3 cm

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8719514338821
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 15.2 cm
- Length: 7 cm
- Width: 7 cm
- Material number (12NC): 929002393149



Issue date: 2024-02-02  
Version: 0.41

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)