

PHILIPS

hue

Outdoor sensor

A

User manual

Benutzerhandbuch

Notice d'emploi

Manual de usuario

Manual do usuário

Manuale d'uso

Incl.

A

B

2 x AA battery

A

B

Excl.

2

1

hue

Hue app

2

A

B

3

!

?

www.philips-hue.com/support

3

3s

4

!

1.5 - 2.5 m

80°

8 - 10 m

5

8 - 10 m

160°

5

!

12m

160°

80°

IP54. The product should not be submerged in water.

alkaline battery (non-rechargeable)

Temperature (operation): -20–50°C

Relative humidity: 5-95% non-condensing

6

4a

4a → 5

4b

4b → 6

7

hue

Signify

I.B.R.S. / C.C.R.I. Numéro 10461

5600 VB Eindhoven,

the Netherlands

00800-74454775

© 2025 Signify Holding

All rights reserved

Last update: 07/2025

www.philips-hue.com

442296620151

4c

4c → 7

4d

4d → 8

8

5

Not incl.

6

6 → 11

9

7

!

8

8 → 11

10

9

!

10

11

11

!

12

1

2

1

2

13

3

4

2 x

14

5

6

1

2

15